

Gardner
Denver[®]

5-25 HP | RECIPROCATING AIR COMPRESSORS

Reward Series





★★★★★

QUICK SHIP*
COMPRESSORS

AVAILABLE FOR

*Immediate
Shipment*

Downtime is NOT an option

Gardner Denver has the solution

Fully-Equipped Packages Available Immediately


A Winning Combination

Gardner Denver compressors are proven units, known for their reliability over decades of use. We know our products and understand how they operate in many different operating environments. No matter the application, Gardner Denver gets the job done.

The Reward Program features fully-equipped compressor packages that are available for immediate shipment.

We Provide the Total Package



Premium accessories on a superior performing compressor—saves you time and protects your investment.



*Immediate shipment subject to unit availability.

Reward Standard Features

- Heavy Duty Two-Stage, Splash-Lubricated Air Compressor Pump(s)
- Multi-Finned Cylinders and Head
- Integral Cylinder Head
- Intercoolers for Cooling Between Stages
- Reliable High Flow Disc Valves
- Tapered Roller Main Bearings
- Balanced Crankshaft
- Oil-Level Site Glass
- Centrifugal Unloader for Loadless Starting
- 0-300 PSIG Air Pressure Gauge
- Factory Fill with AEON Lubricants
- Vertical or Horizontal Configurations
- ASME Code Air Receiver
 - Pressure Relief Valve
 - Service Valve
 - Drain Valve
 - Pressure Gauge
- Oversized Inlet Filter
- Mounted Control Panel
- Electric Timed Drain
- Air-Cooled Aftercooler (select models)
- Vibration Isolators
- Low-Oil Stop Control



*Duplex available in 5, 7.5 and 10 HP. Double CFM values for Duplex Units.


ISOLATOR PADS



Vibration Isolator Pads

Isolates the compressor unit from the foundation or floor. Reduces noise and protects the unit from out-of-level floor situation that could cause vibration and damage.

AIR-COOLED



Air-Cooled Aftercooler

The factory mounted, heavy duty, air-cooled aftercooler effectively removes up to 65% of the moisture from discharged compressed air.

CONTROL PANEL



Control Panel

Provides thermal overload protection, and transformer provides reliable low voltage output to the auxiliary components. May be mounted or unmounted.


TANK DRAIN



Automatic Tank Drain

An adjustable electric timed drain automatically discharges moisture from the receiver.

LOW OIL MONITOR



Low Oil-Stop Control


Low oil-stop control shuts down the unit when oil levels are below an adequate level. Prevents the unit from restarting until oil level has been restored.

*Unit shown with optional field install hour meter and test/off/auto switch.



GARDNER DENVER
PREMIUM ACCESSORIES
INCLUDED

Convenience & Peace of Mind



Standard Warranty

The standard warranty covers parts and labor on the package components for one year and three years on the compressor pump.



The Gardner Denver philosophy ensures long-lasting, reliable equipment. Our warranty program demonstrates our confidence in our products. Each new Gardner Denver assembled unit has a 3 year warranty on the compressor pump against defects in materials of workmanship under normal use and service.

*See standard warranty form BU-51 for complete standard warranty details.

Premium Extended Warranty

Purchase a Premium Warranty Kit at the same time as your new Gardner Denver compressor package to receive extended warranty protection. This offer will double the coverage with an additional 3 years of warranty on the compressor pump (parts & labor) providing 6 YEARS of worry free coverage. The Premium Extended Warranty also provides an extra 12 months coverage on the package for a total of 24 months. See Premium Warranty form BU-60 for complete extended warranty details.

- Premium Warranty kit has all necessary service items (oil & filters) for 6 years of annual maintenance.
- Duplex machines require two kits, one for each pump.
- The use of approved Gardner Denver lubricants are required to maintain the extended warranty period.



Reward

5-25 HP RECIPROCATING COMPRESSORS

MOTOR HP	TANK CAPACITY	REWARD MODEL	DIMENSIONS L x W x H	APPROX. SHIP WEIGHT	175 PSI RATING	
	GAL.		INCHES	LBS.	RPM	CFM DEL'Y
5	80	VR5-8	35 x 27 x 75	590	737	17.0
5 (x2)	120	HR5D-12	75 x 33 x 54	980	737	34.0
7.5	80	VR7F-8	31 x 24 x 75	630	949	22.3
7.5 (x2)	120	HR7D-12	83 x 34 x 54	1305	570	51.2
10	120	HR10-12	71 x 32 x 55	895	718	33.8
10	120	VR10-12	43 x 30 x 81	895	718	33.8
10 (x2)	240	HR10D-24	88 x 38 x 61	2325	718	67.6
15	120	HR15-12	73 x 36 x 62	1210	776	54.1
25	120	HR25-12	74 x 36 x 65	1597	776	90.7

Sales & Service Distributors Across America

An Extensive Network

Your sales, service and technical support needs will be handled quickly and easily by our extensive network of Gardner Denver factory-trained, authorized local distributors. Maintaining and adequately servicing your compressor has never been easier.



To find a distributor visit:
gardnerdenver.com

The leader in every market we serve
by continuously improving all business processes
with a focus on innovation and velocity

Gardner

Denver[®]

1800 Gardner Expressway
Quincy, IL 62305
www.gardnerdenver.com



©2024 Industrial Technologies and Services, LLC
Printed in U.S.A.
GR-REWARD 3rd Ed. 6/24

