

ELECTRA TS/TSV 200-300 HP ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR		50 Hz				60 Hz				NOISE LEVEL ¹ ENCLOSED/ UNENCLOSED	WEIGHT ²		DIMENSIONS L x W x H
			NOMINAL PRESSURE		FAD		NOMINAL PRESSURE		FAD					
	HP	KW	PSIG	BAR	ACFM	M ³ /MIN	PSIG	BAR	ACFM	M ³ /MIN		DB(A)	LBS	
ETS-200	200	150	100	6.9	1092	30.94	100	6.9	1159	32.81	80/93	10924	4955	129 x 92 x 76 (3277 x 2337 x 1930)
			125	8.6	1057	29.93	125	8.6	1062	30.08				
			200	13.8	839	23.76	200	13.8	835	23.65				
ETS-250	250	185	100	6.9	1375	38.93	100	6.9	1404	39.75	80/93	11522	5226	
			125	8.6	1285	36.38	125	8.6	1298	36.77				
			200	13.8	1048	29.68	200	13.8	1053	29.82				
ETS-300	300	225	100	6.9	1639	46.42	100	6.9	1632	46.21	80/93	12040	5461	
			125	8.6	1526	43.22	125	8.6	1526	43.22				
			200	13.8	1164	32.97	200	13.8	1248	35.35				
ETSV-150	200	150	100	6.9	1178	33.37	100	6.9	1178	33.37	80/93	11179	5071	
			145	10.0	1011	28.62	145	10.0	1011	28.62				
			200	13.8	834	23.6	200	13.8	834	23.6				
ETSV-185	250	185	100	6.9	1418	40.14	100	6.9	1418	40.14	80/93	11755	5332	
			145	10.0	1227	34.74	145	10.0	1227	34.74				
			200	13.8	1057	29.94	200	13.8	1057	29.94				
ETSV-225	300	225	100	6.9	1652	46.79	100	6.9	1652	46.79	80/93	11954	5422	
			145	10.0	1452	41.10	145	10.0	1452	41.10				
			200	13.8	1223	34.65	200	13.8	1223	34.65				

1) Noise levels are for enclosed/unenclosed air-cooled models.

2) Weights and dimensions are for air-cooled unenclosed models.