

Technical Data

Gardner Denver Model	FAD	Inlet Connection	Outlet Connection	Dimensions			Weight	Service Kits
	(m ³ /min)	(inch)	(inch)	Width	Depth	Height	(kg)	
GDSEP020	3.5	½	½	255	230	239	3.2	SEP020
GDSEP035	3.5	½	½	395	210	385	8	SEP035
GDSEP050	5	½	1	580	190	610	11.1	SEP050
GDSEP100	10	½	1	650	240	750	17.6	SEP100
GDSEP200	20	½	1	780	305	900	31.6	SEP200
GDSEP300	30	½	1	970	380	900	47.5	SEP300
GDSEP600	60	½	1	1160	580	1040	74	SEP600